


LUTINA CVf



Specifications		Specifiable range / Availability
Prescription	Size reduction	Optimum value by balanced thickness processing
	Prism	Up to 3 prism (3C & 5C: Please ask to our CS center)
	Decentration	Not available
	Base curve selection	Available from 3C or 5C
	Color	Available (Please refer "available color list")
	LUTINA Photochromic	Gray, Brown
Individual	Wrap angle (Default value: 0.0°)	0.0° ~ 15.0° (0.1°steps)
Frame data	Slice (Frame shape required)	Optimum value by balanced thickness processing Available for plus & mixed power lenses
	Balanced thickness processing	Standard
	Remote edging	Available
	Fine edge processing	Available (Less S+C = -3.00 : Not available)