


# LUTINA CVf



Specifications		Specifiable range / Availability
Prescription	Size reduction	Optimum value by balanced thickness processing
	Prism	Up to 3 prism (3C & 5C: Please ask to our CS center)
	Decentration	Not available
	Base curve selection	Available from 3C or 5C
	Color	Available (Please refer "available color list")
Individual	Wrap angle (Default value: 0.0°)	0.0° ~ 15.0° (0.1°steps)
Frame data	Slice (Frame shape required)	Optimum value by balanced thickness processing Available for plus & mixed power lenses
	Balanced thickness processing	Standard
	Remote edging	Available
	Fine edge processing	Only available more than -3.00D.