



LUTINA HR / LUTINA HR (N)



Specifications		Specifiable range / Availability
Prescription	Size reduction	by 50mm Min : only (+), 1mm step
	Prism	Up to 3 prism
	Decentration	Not available
	Base curve selection	Please refer available curve range list
Individual parameters	LUTINA Photochromic	Gray, Brown, Only for LTN-P 1.60 HR Surf Blue
	Wrap angle (Default value: 0.0°)	0.0° ~ 15.0° (0.1°steps)
	Tilt angle (Default value: 8.0°)	-5.0° ~ 25.0° (0.1°steps)
	Vertex distance (Default value: 12.0mm)	8.0mm ~ 25.0mm (0.1mm steps)
	Slice (Frame shape required)	Available for plus & mixed power lenses
Frame data	Remote edging	Available
	Fine edge processing	Only available more than -3.00D.

Lens mark	
A	Fitting point Geometrical center and area to measure the prismatic power
B	Identification mark
C	If i Location Mix is specified, the i mark will be engraved.
D	Location mark

LTN1.76	
Regular-use	Near-vision
LTN1.67	
Regular-use	Near-vision
LTN1.60	
Regular-use	Near-vision

LUTINA PHOTO available only Regular-use type