



HR-W (C) / (CN) / (S)

(C) : Emphasis on visibility type
 (CN) : Emphasis on visibility type · For near-vision
 (S) : Emphasis on thinness type

※The lens may be a cataract lens depending on the power



Specifications	Specifiable range / Availability
Prescription	Size reduction by 50mm Min : only (+), 1mm step
	Prism Up to 3 prism
	Decentration Not available
	Base curve selection Please refer available curve range list
Individual parameters	Wrap angle (Default value: 0.0°) 0.0° ~ 15.0° (0.1°steps)
	Tilt angle (Default value: 8.0°) -5.0° ~ 25.0° (0.1°steps)
	Vertex distance (Default value: 12.0mm) 8.0mm ~ 25.0mm (0.1mm steps)
Frame data	Slice (Frame shape required) Available for plus & mixed power lenses
	Remote edging Available
	Fine edge processing Only available more than -3.00D.

Lens mark	
A	Fitting point Geometrical center and area to measure the prismatic power
B	Identification mark
C	If i Location Mix is specified, the i mark will be engraved.
D	Location mark

1.76 HR-W Emphasis on thickness type (S)	Emphasis on visibility type (C)	Emphasis on visibility type for near-vision (CN)
1.70 HR-W Emphasis on thickness type (S)	Emphasis on visibility type (C)	Emphasis on visibility type for near-vision (CN)
1.67 HR-W Emphasis on thickness type (S)	Emphasis on visibility type (C)	Emphasis on visibility type for near-vision (CN)
1.60 HR-W Emphasis on thickness type (S)	Emphasis on visibility type (C)	Emphasis on visibility type for near-vision (CN)